

PRODUCT DATA SHEET

# AMBERLITE™ UP252

## Semiconductor Grade Strong Acid Cation Exchange Resin for Industrial Use

AMBERLITE UP252 resin is a semiconductor grade strongly acidic cation exchanger. The matrix is based on macroporous crosslinked polystyrene and the functional groups are sulphonates. Due to the very high quality of the raw materials and the cleaning procedure carried out at the end of the

manufacturing process, this resin can be used as a component of mixed beds for the production of ultra-pure water. In this application, AMBERLITE UP252 resin is combined with AMBERLITE UP900 resin.

---

### PROPERTIES

---

Matrix _____	Styrene divinylbenzene copolymer
Functional group _____	Sulphonic acid
Ionic form as shipped _____	H <sup>+</sup>
Total exchange capacity <sup>[1]</sup> _____	≥ 1.7 eq/L (H <sup>+</sup> form)
Moisture holding capacity <sup>[1]</sup> _____	52 to 58 % (H <sup>+</sup> form)
Shipping weight _____	800 g/L
Particle size	
Uniformity coefficient _____	≤ 1.6
Harmonic mean size _____	0.600 – 0.800 mm
< 0.300 mm <sup>[1]</sup> _____	0.1 % max

<sup>[1]</sup> *Contractual value*  
*Test methods are available on request.*

---

### SUGGESTED OPERATING CONDITIONS

---

Composition in volume _____	40 % AMBERLITE UP252 60 % AMBERLITE UP900
Service flow rate _____	10 to 30 BV*/h
Linear velocity _____	15 to 40 m/h
Bed depth _____	About 1.50 m for the whole mixed bed
Regeneration	
Regenerant _____	HCl : 4 - 6 %
First regeneration _____	200 g/L
Following regenerations _____	100 to 150 g/L
Flow rate _____	1 to 5 BV/h
Temperature _____	15 to 25°C
Slow rinse _____	2 BV at regeneration flow rate

\* 1 BV (Bed Volume) = 1 m<sup>3</sup> solution per m<sup>3</sup> resin

## COMMISSIONING

At the time of commissioning it is recommended to follow the procedure described in our brochure : Startup procedure for regenerable ultra pure mixed beds.

## LIMITS OF USE

AMBERLITE UP252 resin is suitable for industrial uses. For other specific applications such as pharmaceutical, food processing or potable water applications, it is recommended that all potential users seek advice from Rohm and Haas in order to determine the best resin choice and optimum operating conditions.

**All our products are produced in ISO 9001 certified manufacturing facilities.**

Rohm and Haas/Ion Exchange Resins - Philadelphia, PA - Tel. (800) RH AMBER - Fax: (215) 409-4534  
Rohm and Haas/Ion Exchange Resins - 75579 Paris Cedex 12 - Tel. (33) 1 40 02 50 00 - Fax : 1 43 45 28 19

<http://www.amberlite.com>



*AMBERLITE is a trademark of Rohm and Haas Company and its affiliates, Philadelphia, U.S.A.*

*Ion exchange resins and polymeric adsorbents, as produced, contain by-products resulting from the manufacturing process. The user must determine the extent to which organic by-products must be removed for any particular use and establish techniques to assure that the appropriate level of purity is achieved for that use. The user must ensure compliance with all prudent safety standards and regulatory requirements governing the application. Except where specifically otherwise stated, Rohm and Haas Company does not recommend its ion exchange resins or polymeric adsorbents, as supplied, as being suitable or appropriately pure for any particular use. Consult your Rohm and Haas technical representative for further information. Acidic and basic regenerant solutions are corrosive and should be handled in a manner that will prevent eye and skin contact. Nitric acid and other strong oxidising agents can cause explosive type reactions when mixed with Ion Exchange resins. Proper design of process equipment to prevent rapid buildup of pressure is necessary if use of an oxidising agent such as nitric acid is contemplated. Before using strong oxidising agents in contact with Ion Exchange Resins, consult sources knowledgeable in the handling of these materials.*

*Rohm and Haas Company makes no warranties either expressed or implied as to the accuracy or appropriateness of these data and expressly excludes any liability upon Rohm and Haas arising out of its use. We recommend that the prospective users determine for themselves the suitability of Rohm and Haas materials and suggestions for any use prior to their adoption. Suggestions for uses of our products of the inclusion of descriptive material from patents and the citation of specific patents in this publication should not be understood as recommending the use of our products in violation of any patent or as permission or license to use any patents of the Rohm and Haas Company and its affiliates. Material Safety Data Sheets outlining the hazards and handling methods for our products are available on request.*